

Clip Pad



Technische Daten

Technical data

Mindesthaltbarkeit	8 Monate
Minimum durability	8 months

Mechanische Daten

Mechanical data

Abmessung	72 x 66 x 2 mm
Dimensions (lxbxh)	

Gewicht	5 g
Weight	

Auslösekraft	240 g
Release force	

Benutzerumgebung

Environmental condition

Betriebstemperatur	0 °C – 48 °C
operating temperatur	

IP Klasse	IP 65
IP class	

Artikelnummer	520324
Article number	

Produktbeschreibung / Anwendung

Product description / usage

Mit dem Clip Pad kann der HS 50 an einem Umhängeband oder Zipper befestigt werden. Ausgelöst wird der Scanner des HS 50 durch den Touch – Screen oder den Taster am Clip Pad.

The Clip Pad is designed to be used with a lanyard or a zipper. Scanning can be activated by tapping the touch screen or the trigger of the Clip Pad.

Clip Pad Montageanleitung

Clip Pad mounting instructions

Das Clip Pad mit 3 Schrauben und 3 Beilagscheiben, wie in der Abbildung unten, am HS 50 montieren.

Anzugsmoment: 0,3 Nm

Please, assemble the Clip Pad with the 3 provided screws and discs, shown in the figure below, to the HS 50.

Torque: 0.3 Nm

